


PLENUM CABLE		
FIBERS	CABLE TYPE	DIA. (INCHES)
12	SMALL DIA. INDOOR	.19
24	SMALL DIA. INDOOR	.21
48	SMALL DIA. INDOOR	.22
72	SMALL DIA. INDOOR	.26
96	SMALL DIA. INDOOR	.32
144	SMALL DIA. INDOOR	.37


- NOTES:
- VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A LIST OF CURRENT PARTS APPLICABLE FOR USE WITH THIS PRODUCT.
 - ALL MATERIALS AND COMPONENTS USED MEET THE MATERIAL RESTRICTIONS OF RoHS (EUROPEAN DIRECTIVE 2011/65/EU ON THE RESTRICTION OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE RoHS TECHNICAL ADAPTATION COMMITTEE.
 - SINGLEMODE MPO AND SINGLEMODE PANMPO ARE ANGLED POLISH (APC)



TRANSITIONS	
HD FLEX	
STANDARD TUBE	VARIOUS STYLES

SEE "SERIAL" COLUMN IN TABLE LOCATED ON SHEET 2.

CONNECTORS	
12F FEMALE MPO	
12F MALE MPO	
12F FEMALE PANMPO	
12F MALE PANMPO	
24F FEMALE MPO	
24F MALE MPO	



TYPICAL PULLING EYE

NOMINAL PULLING EYE DIAMETERS FOR PANMPO/MPO TRUNKS	
FIBERS	INCHES
12	1.1"
24	1.1"
48	2.1"
72	2.1"
96	2.1"
144	2.1"
PIGTAILS	1.1"

FOR PIGTAILS ONLY

METHOD A FIBER COLOR KEY	METHOD B FIBER COLOR KEY
FIBER 1 - BLUE	FIBER 1 - AQUA
FIBER 2 - ORANGE	FIBER 2 - ROSE
FIBER 3 - GREEN	FIBER 3 - VIOLET
FIBER 4 - BROWN	FIBER 4 - YELLOW
FIBER 5 - SLATE	FIBER 5 - BLACK
FIBER 6 - WHITE	FIBER 6 - RED
FIBER 7 - RED	FIBER 7 - WHITE
FIBER 8 - BLACK	FIBER 8 - SLATE
FIBER 9 - YELLOW	FIBER 9 - BROWN
FIBER 10 - VIOLET	FIBER 10 - GREEN
FIBER 11 - ROSE	FIBER 11 - ORANGE
FIBER 12 - AQUA	FIBER 12 - BLUE

SINGLEMODE METHOD A AND METHOD B PANMPO ARE NOT POLARITY REVERSIBLE.

PART NUMBER: SEE CONFIGURATOR ON SHEET 2

TITLE: CONFIGURE TO ORDER 12F TO 144F MPO/PanMPO TRUNK PLENUM CABLES

CUSTOMER DRAWING

ITEM REVISION NAME: 01608AAC/00

DATASET FILE NAME: 01608AAC_DC/00D

MATERIAL: MULTIPLE

DRAWING NUMBER: 01608AAC-DC

THIRD ANGLE PROJECTION

DRAWN BY: JSP, DATE: 10/28/19, CHK: FJDU, SCALE: NONE


SHEET 1 OF 2

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
00D	5/30/23	JSP	FJDU	EJH	D. REMOVED OM5 FROM DRAWING, SEE 01608AAH-DC.	0160AAC-DC
00C	04-10-23	SAT	FJDU	EJH	C. ADDED ADDED, 008 STANDARD PIGTAIL WITHOUT PULLING EYE. B. ADDED METHOD FIBER COLOR KEY TABLES	0160AAC-DC
00B	11-18-20	SAT	FJDU	EJH	A. CORRECTED OPTIMIZED TYPO.	0160AAC-DC
00A	10/29/19	JSP	FJDU	EJH	INITIAL RELEASE	0160AAC-DC

B-SIZE CUSTOMER

CHARACTER	1	2	3	4	5	6	7	8	9-11	12	13-15
ATTRIBUTE	FIBER	PRODUCT/CABLE TYPE	FIBER TYPE	FIBER COUNT	FLAME RATING	CONNECTOR TYPE (END 'A')	CONNECTOR TYPE (END 'B')	POLARITY/PERFORMANCE	SERIAL	UNITS	LENGTH (TIP TO TIP)
OPTIONS	F	Y= SMALL DIA INDOOR TRUNK	9= SM	T= 12F	P= PLENUM (OFNP)	5= 12F MPO, FEMALE	5= 12F MPO, FEMALE	A= POLARITY A- STANDARD IL	XXX= SEE TABLE BELOW	F= FEET	015 - 999 FEET 5 - 400 METERS
			S= OM4+	U= 24F		6= 12F MPO, MALE	6= 12F MPO, MALE	B= POLARITY B- STANDARD IL		M= METERS	
			X= OM3	W= 48F		7= 12F PANMPO, FEMALE	7= 12F PANMPO, FEMALE	K= POLARITY A- ULTRA LOW IL			
			Z= OM4	X= 72F		8= 12F PANMPO, MALE	8= 12F PANMPO, MALE	L= POLARITY B- ULTRA LOW IL			
				Y= 96F		E= 24F MPO, FEMALE	E= 24F MPO, FEMALE	X= POLARITY A- OPTIMIZED IL			
				A= 144F		F= 24F MPO, MALE	F= 24F MPO, MALE	Y= POLARITY B- OPTIMIZED IL			
					U= PIGTAIL						

"SERIAL" COLUMN FROM ABOVE					
SERIAL #	TRANSITION TYPE	BREAKOUT A LENGTH	BREAKOUT B LENGTH	PULLING EYE	DESCRIPTION
001	HD FLEX	1 METER	1 METER	END A ONLY	HD FLEX WITH PULLING EYE
002				NONE	HD FLEX WITHOUT PULLING EYE
003			NONE	END B ONLY	HD FLEX PIGTAIL WITH PULLING EYE
005	STANDARD		1 METER	END A ONLY	STANDARD WITH PULLING EYE
006				NONE	STANDARD WITHOUT PULLING EYE
007			NONE	END B ONLY	STANDARD PIGTAIL WITH PULLING EYE
008			NONE	NONE	STANDARD PIGTAIL WITHOUT PULLING EYE

PART NUMBER		SEE CONFIGURATOR ABOVE	
TITLE			
CONFIGURE TO ORDER 12F TO 144F MPO/PanMPO TRUNK PLENUM CABLES			
CUSTOMER DRAWING			
ITEM REVISION NAME		01608AAC/00	
DATASET FILE NAME		01608AAC_DC/00D	
		THIRD ANGLE PROJECTION	
MATERIAL		MULTIPLE	
DRAWING NUMBER		01608AAC-DC	
DRAWN BY	DATE	CHK	SCALE
JSP	10/28/19	FJDU	NONE
SHEET 2 OF 2			B

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
					SEE REVISIONS ON SHEET 1	0160AAC-DC

B-SIZE CUSTOMER